

KIT CONTENTS

Müller

ID	Name	NO
A	Body lift	2
B	Front mounting hardware	2

C

a1 a2 a3 x1

D

x1

E

Set of cover caps (229525/229524)

x8

(190133) 4x35 mm

G

x8

(190247) 4x13 mm

F

x8

(190133) 4x35 mm


MOUNTING OPTIONS

I

II

III

In this mounting option, the lift mechanism should be shifted down by 21 mm to avoid contact with the front.



INSTALLATION STEPS

WARNING

Don't press down on lever if the front is not be installed, to avoid injury and damage to the lift.

1 Marking the front for the fittings

2 Installing the fittings on the front

3 Install template (select the template number according to your mounting option)

4 Position the lift mechanisms using the templates

5 Lifts installation

6 Remove the template

7 Remove the safety clip

8 Pull out the arm

9 Front installation

12 Opening angle adjustment (80-100°)

When the door height is from 650-800 mm, adjust the opening angle stop to 90°.

13 Soft close speed adjustment

Adjust it slowly to avoid failure of the adjustment function caused by excessive speed.

10 Adjusting the opening force

14 Installing the cover caps

11 3D adjustment of front

After 3D adjustment, turn this screw to fix the fitting.

DISASSEMBLY

1

2

3

4

5

WARNING

Don't press down on lever if the front is not be installed, to avoid injury and damage to the lift.

Elevon 3000 Product Selection Chart (18mm)

Model: S / M / L / XL

LF = Section height KH (mm) × (handle weight × 2 + front weight) FW (kg).

If 2 models are suitable, selects the larger model

LF (power factor)	S:660-1800	KH300: 2.2-6.0KG	M:1100-2900	KH300: 3.7-9.6KG	L:1840-5200	KH350: 5.3-14.8KG	XL:4000-9000	KH450: 8.9-20.0KG	
		KH350: 1.9-5.1KG		KH350: 3.2-8.2KG		KH400: 4.6-13.0KG		KH500: 8.0-18.0KG	
		KH400: 1.7-4.5KG		KH400: 2.8-7.2KG		KH450: 4.0-11.5KG		KH550: 7.2-16.3KG	
		KH450: 1.5-4.0KG		KH450: 2.5-6.4KG		KH500: 3.7-10.4KG		KH600: 6.7-15.0KG	
		KH500: 1.3-3.6KG		KH500: 2.2-5.8KG		KH550: 3.4-9.4KG		KH650: 6.1-13.8KG	
				KH550: 2.0-5.2KG		KH600: 3.0-8.6KG		XL:4000-8400	KH700: 5.7-12.0KG
				KH600: 1.8-4.8KG		KH650: 2.8-8.0KG			KH800: 5.0-10.5KG
						KH700: 2.6-7.4KG			

[illegible]

Elevon 3000 Product Selection Chart (16 mm)

Model: S / M / L / XL

$$\text{LF} = \text{Section height KH (mm)} \times (\text{handle weight} \times 2 + \text{front weight}) \text{ FW (kg)}$$

If 2 models are suitable, selects the larger model

[illegible][illegible]

Elevon 3000 Product Selection Chart (22 mm)

Model: S / M / L / XL


$$\text{LF} = \text{Section height KH (mm)} \times (\text{handle weight} \times 2 + \text{front weight}) \text{ FW (kg)}$$

If 2 models are suitable, selects the larger model

[illegible]

Section width (front density: 720 kg/m³), mm										Section depth > 260 mm										Section height KH (mm)							
1800	1700	1600	1500	1450	1400	1350	1300	1250	1200	1150	1100	1050	1000	950	900	850	800	750	700	650	600	550	500	450	400	350	
M	M	M	M	M	M	M	M	S	S	S	S	S	S	S	S	S	S	S	S	S	S	S	S			300	
								M	M	M	M	M	M	M	M	M	M	M	M	M	M	M	M	M	M		M
L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	S	S	S	350	
								L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L		L
L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	S	S	S	400	
								L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L		L
XL	XL	XL	XL	XL	XL	XL	XL	L	L	L	L	L	L	L	L	L	L	L	L	L	L	L	S	S	S	450	
								XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL		XL
XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	S	S	S	500	
								XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL		XL
XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	M	M	M	550	
								XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL		XL
			XL	XL	XL	XL	XL			XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	M	M	M	600	
								XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL		XL
							XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	L	L	L	650	
								XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL		XL
								XL	XL	XL		XL	XL	XL	XL	XL	XL	XL	XL	L	L	L	L	L	L	700	
								XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL	XL		XL
																	XL	XL	XL	XL	XL	XL	L	L	L	800	

INSTALLATION INSTRUCTION MULLER ELEVON 3000



viyar

0 (800) 100 100 | viyar.eu

RELIABLE FITTINGS ARE DURABLE FURNITURE